



innovate | create | support

## DX-CD2 Disc Destruction Device



The DX-CD2™ Second Generation DX-CDe Destruction Device is the newest generation of CD-ROM and DVD destruction devices produced by the industry leader in the field of optical digital data destruction.

The DX-CD2™ design specification requires the data layer of optical drives to be ground to 250 microns – eliminating forensic recovery of data by any known means. The DX-CD2™ incorporates two speed options: Setting one is defaulted to an 18 second cycle time or @ 180 discs per hour. Setting two is programmable upon request to permit from 90-340 discs to be destroyed per hour. The DX-CD2™ is lightweight, quiet enough for an office environment, safe, clean and inexpensive to operate.

Your organization can be assured that your digital information has been permanently and safely destroyed. With current regulations, any person or company that does not properly dispose of digital records faces a major liability. Join the thousands of customers who sleep at night knowing their digital records are no longer in use and can never be used again.

The DX-CD2™ has been evaluated by the NSA and can be used to sanitize TS/SCI CD-ROMs until July 2027". Additionally, the DX-CD2 meets the requirements of the Canadian Royal Mounted Police (RCMP) for listing in the G1-001 Security Equipment Guide (SEG) as an approved device for the destruction of all Classified and Protected information on optical media when used in accordance with the operating instructions. This product is designed with the high-security sector in mind and follows the high-quality standards used in the Department of the Defense (DoD) product line for classified data destruction.

### Features

- Fast Operation – under 18 seconds per disc
- Technology process results in digital data 100% beyond forensic recovery
- Meets NSA/CSS 04-02 for CD-ROM until July 2027
- Environmentally Safe – dust is collected in bag to be safely disposed of
- Easy to Use Push button operation
- Information layer is ground to 250 microns